

Instructions: Cosmetic bag made from coated cotton

Instructions No. 1239

This beautiful **cosmetic bag** is not only **practical when travelling**, but also a real **eye-catcher** in every bathroom. The fabric from which the bag is sewn is **water-repellent and washable** - so your treasures are **well protected and beautifully packed**. You can find out how to **sew** this trendy bag very easily here.



And it's that easy:

First cut the fabrics **according to the templates**. Two cuts for the **outer fabric**, **two** cuts for the inner fabric **and the** desired stars

Now place an inner and an outer fabric **right on top** of each other and push one half of the 35 cm long zipper **in between**. The rounding is now closed with the **straight stitch** - this way you have sewn the zipper and the two fabrics together

Repeat this process with the second half of the zipper and the remaining fabric cuts

Now unfold the **pocket sections** first and then lay them on top of each other so that the inner and outer fabrics are placed **right** sides together.

So there should be a **square with cut corners in front of** you. Gradually close all sides with the straight stitch and **leave out a turning opening on the long side of the inner fabric**.

Next, the **corners are closed**. To do this, take a corner in your hand and pull it apart so that a **straight edge is created and the seams of the long sides are in the middle**. Now close the corner again with the straight stitch **and** proceed in this way with the other corners of the cosmetic bag

Now you can **turn the bag**

Next, topstitch **the turning opening with the straight stitch and** then put the inside into the outside pocket. Finally, glue the **stars** with the **fabric adhesive** - and your new cosmetic bag is ready!

Article information:

Article number	Article name	Qty
111324	Fabric/Textile glue	1
391214	Gütermann sewing thread set "All-purpose sewing thread", 7 x 100 m	1
36202301	Prym scissors Professional tailor scissors	1
360296	Glass head-Pins Prym, 48 mm	1